



②! Pin screw for additional locking of the fiber ferrule:
 - before pulling the FC-connector:
 unlock the pin screw.
 - before inserting the FC-connector:
 make sure the ferrule receptacle is not blocked
 by the pin screw !



Thrust and tension screw (3x120°)
 for tilt adjustment
 with hex key wrench size 1.5mm
 50HD-15 ①





Thrust screw M3 max.torque 50Ncm

Tension screw M2 max.torque 40Ncm

Tools for assembly and adjustment

hex-key size 1.5mm 50HD-15
 screw driver size 1.2mm 9D-12

① ②



For information only
 Not for manufacturing purposes

Dimensions DIN EN ISO 14405		Scale: 2:1			
		Date		Name	
		08.04.2020		Trapp	
		editor			
		exam.			
		free			
		19.5AC-0-FC		19.5AC-0-FC	
		FC Adapter w/o Optics, System Mount Ø 19.5 mm		FC Adapter w/o Optics, System Mount Ø 19.5 mm	
		Customer Drawing		Customer Drawing	
		Schäfter+Kirchhoff OPTICS, METROLOGY, AND PHOTONICS		79709-2052-0620	
		File: 970920520620.idw		Model: 970920520620.iam	
				Size: A3	
				Page: 1	